

**Power supply for  
door communication 24 V DC 700 mA**  
2570 00

# GIRA


Gira  
Giersiepen GmbH & Co. KG  
Elektro-Installations-  
Systeme  
Postfach 1220  
42461 Radevormwald  
Deutschland  
Tel +49 (0) 21 95 / 602 - 0  
Fax +49 (0) 21 95 / 602 - 191  
[www.gira.de](http://www.gira.de)  
[info@gira.de](mailto:info@gira.de)

10 41 09 13 20/11

# GIRA

## Device description

The power supply for door communication 24 V DC is used as power supply for the video terminal.



## Connection and installation




### Attention

Installation and mounting of electrical devices may only be carried out by a qualified electrician.

For installation protected from dripping and sprayed water, the power supply is mounted on a top-hat rail in the distribution.

The ventilation slits of the power supply must not be blocked.

The VideoTerminal is connected with screw terminals as shown in the illustration.



## Technical data

Primary rated voltage: 230 V AC, 50/60 Hz

Secondary rated voltage: SELV 24 V DC

Secondary rated current: 0.7 A

Fuse: self-resetting electronic short-circuit protection

Dimensions: DRA with 6 modules

Temperature range: 5 °C to + 40 °C

Protection type: IP 20

## Warranty

The warranty is provided in accordance with statutory requirements via the specialist trade.

Please submit or send faulty devices postage paid together with an error description to your responsible salesperson (specialist trade/installation company/electrical specialist trade).

They will forward the devices to the Gira Service Center.